

Introduction

The M-PGWMS(OM) is made with the appropriate groove to fetch M-SHOM style sample plates. In its standard version, angular degree of freedom of the sample plate held by the pincer allows for dangling of the sample. Exact values for the clearance of the sample plate are given in the drawing. For a firmer grip of the plate, please specify the (OMH) option. In combination with MDG dual shaft linear-/rotary feedthroughs, the (OMH) option is recommended.

Adds 27.0mm to dimension Y of the main product

Description	Part Code
Straight pincer grip for M-SHOM flag style sample plates	M-PGWMS(OM)
Hard grip straight pincer grip for M-SHOM flag style sample plates	M-PGWMS(OMH)

Specifications:

Materials

Stainless steel 1.4301

Berylco 25

Vacuum Range

atm to 1×10^{-11} mbar

Bakeout Temperature *

150°C max.

Jaw Opening

35°






Standard clearance, play of

+/- 8°

Hard version clearance, play of

+/- 2°







general tolerances ISO 2768-K

Material: all UHV compatible		nominal over		1	6	30	100	300	1000
Straight pincer grip (hard grip) for SHOM sample plates		dimension up to		6	30	100	300	1000	2000
		tolerance ±		0.05	0.1	0.3	0.5	0.8	1.2
PG		Scale		Drawn		Denys Sutter			
Ferrovac GmbH CH-8050 Zurich		1:1		Date		01.03.2011			
				changed		14.07.2022 CW			
				PGWMS (OMH) sheet 1/2					
		Rev.	D						